


1532nm Benchtop Single-Mode SLD Light Source 3mW



Product Description

Idealphotonics'Ultra-Width series 1550nm high-stability single-mode pump source utilizes a TEC-stabilized single-mode semiconductor laser, offering wavelength stability and high output power. Based on an advanced microprocessor control system combined with high-precision ATC and ACC (APC) control circuits, it achieves highly stable laser output while ensuring quick and intuitive operation of the light source. We can also provide corresponding communication interfaces and control software based on user requirements to enable computer control. This light source features a Turn-Key pump laser protection function to effectively prevent user errors. It supports coarse power adjustment (1mW steps) and fine power adjustment (0.1mW steps).1550nm single-mode pump source is a highly integrated desktop system light source with a high-definition LCD display, continuously adjustable output power, and synchronous current and voltage display, making it ideal for experimental scientific research and production testing. Additionally, the company can provide modular packaging based on user needs for easy system integration.









Part Number

LP-SLD-1532-B-3-40-SM

Product features

Single-mode high-power output: up to 25mW Spectral width up to 80nm ASE optical isolation protection design Stable and continuously adjustable output power LCD status display High-precision ACC and ATC control circuits. Optional built-in isolator

Application area

Fiber optic gyroscope Optical coherence testing Test and measurement Nonlinear effect research

Parameters

Parameters	Unit	Specs			
		Min.	Тур.	Max.	
PN#		LP-SLD-1550-B LP-SLD-1550-M*			
Output Power	mW	3	-	5	
Peak Operating Wavelength	nm	1540	1550	1560	
Spectral Width (FWHM)	nm	25	40	80	
Output Side Mode Suppression Ratio (SMSR)	dB	20	-	-	
Output Isolation	dB	-	30	-	
Output Power Stability (15 minutes)	%	-	±0.5	± 1.0	
Output Power Stability (8 hours)	%	-	±1.0	±2.0	










Output Power Adjustable Range	%	0	-	100		
Output Power		Coarse/Fine Adjustment				
Adjustment Mode		coarse/Time / lajustiment				
TEC Stability	${\mathbb C}$	-	\pm 0.1	\pm 0.2		
TEC Operating Range	$^{\circ}\!$	25	30	35		
Operating Voltage	VAC	100	220	240		
Electrical Power	W	_	_	30		
Consumption	VV			30		
Operating	$^{\circ}\!$	0		50		
Temperature	C	U	-	30		
Storage	${\mathbb C}$	-40	_	85		
Temperature	C	40		03		
Output Fiber Type		SM/PM				
Output Fiber	m	> 1				
Length	\(\frac{1}{1}\)					
Output Fiber		FC/APC, other models optional				
Connector						
Dimensions	mm	340(L) $ imes$ 240(W) $ imes$ 100(H) Benchtop				
		150(L) $ imes$ 125(W) $ imes$ 25(H) Module				

Technical Specification Notes

- 1.Output power selectable;
- 2.Peak operating wavelength customizable;
- 3. Isolation refers to the isolation against ASE light;
- 4.Output power stability test conditions: 25° C, tested after a 30-minute warm-up;
- 5.Maximum power consumption refers to the overall power consumption under extreme operating conditions.









^{*}Software remote control optional



Spectrum Graph



Wavelength Stability Test











Beam Quality



Power Test Table



SLD light source power stability test curve



Ordering info

LP-SLD-1550-PG-<OPP>-<BWD>-FT

PG: Packaging Type

B: Benchtop

M: Module

OPP (Output Power): Output power in mW. For example: 10-10mW, 50-50mW

BWD: 25:25nm, 40:40nm, 50:50nm, 60:60nm, 80:80nm, 100:100nm

FT: Fiber Type

SM=SMF-28E+ PM=PM1550





