

10:90 2x2 1550nm Polarization-mode Fiber Coupler




Product Description

These 2x2 Polarization Maintaining (PM) Fiber Couplers are designed for use from 460-2200 nm with selectable coupling ratios of 50:50, 75:25, 90:10, or 99:1. The 2x2 couplers are bidirectional and can be used to split and mix signals (see the 2x2 Coupling Examples tab). PM couplers are manufactured using Panda-type PM fiber, so they maintain a high polarization extinction ratio (PER) when light is launched along the slow axis of the fiber. As shown in the figure to the right, stress rods are parallel to the fiber core and apply stress, creating birefringence in the fiber core, resulting in PM operation. Typical applications for PM couplers include optical sensors, optical amplifiers, and fiber gyroscopes.

Part Number

NIR-FBC-W1550-S22-CR1090-1-9-PA












Product features

980/1064/1550/1310nm polarization-maintaining fiber couplers . Split ratio 50:50, 75:25, 90:10 or 99:1. Bidirectional coupling (either end can be used as input) . 2.0 mm narrow key FC/PC or FC/APC connector . Each coupler includes a separate test report

Application area


Polarization-maintaining fiber amplifier Fiber optic gyroscope Optical sensor



The default alignment mode of Idealphotonics' optical polarization-maintaining components is slow-axis alignment.

Idealphotonics' polarization-maintaining couplers have high extinction ratios and operate over a wide temperature range of -40 °C to 85 °C. Note that PER varies with temperature; see the Temperature Cycling Test Section in the Polarization Extinction Ratio Measurement tab for details. They have a max. power of 1 W with connectors or bare fiber and 5 W when spliced (see the Damage Threshold tab for details). These couplers have been









extensively tested and PER verified; see the Polarization Extinction Ratio Measurement tab for details of the testing process.

Standard couplers feature 2.0 mm narrow key FC/PC or FC/APC connectors as summarized in the table below. When using the coupler as a beam combiner, it is necessary to terminate the fiber to the unused output, as some of the light will propagate through this branch. Fiber pigtails have Ø900 µm Hytrel® jackets and are 0.8 m long. Custom coupler configurations with other wavelengths, fiber types, coupling ratios, alignment axes, or port configurations are also available.

Parameter:


Structure		Unit	1×2/2×2	
Туре			Polarization-Maintaining Fiber optic	
			Coupler(PMFBC)	
Operating wavelength		nm	980 or 1064 or 1310 or 1550	
Operating bandwidth		nm	±15	
Max. Insertion loss	50/50	%	3.60/3.60	
	30/70	%	5.75/2.10	
	10/90	%	11.60/1.00	
	5/95	%	14.80/0.80	
	2/98	%	18.50/0.45	
	1/99	%	22.00/0.40	
Extinction ratio		dB	CR>5%	≥20.00
			5%≥CR>1%	≥18.00
Optical return loss		dB	≥50.00	
Direction		dB	≥55.00	
Operating temperature		Deg.	-5-75	
Storage temperature		Deg.	-40-85	
Fiber length		m	1.00 ± 0.10	
Fiber type			Panda PM Fiber	
Fiber diameter		um	250	900 900/2000/3000
Package size		mm	2.4x25,3×35,3×54	$3\times54 90\times16\times10$

Note:

1. All test results do not include connectors. Adding connectors will increase the loss by 0.3dB.











- 2. We can accept customization for better parameters or other requirements.
- 3. If you need customized wavelength, coupling ratio and connector options.

Single point data test 1X2, 50:50, 1550nm PM fiber coupler (broadband SLD center wave 1550nm, spectrum width: 30nm, 2.5mw polarization-maintaining SLD laser test as an example)




1550nm PM SLD Laser diode



Slow axis alignment

NIR-PMFBC - W1550-S1-CR5050-1-9-PA-35T

black port@1550nm



NIR-PMFBC - W1550-S1-CR5050-1-9-PA-35T white port@1550nm











Ordering Info:

NIR-PMFBC - W□□□□-So-CR▽-☆-△-XX-□□

Wood: Wavelength

1064:1064nm

1310:1310nm

1392:1392nm

1512:1512nm

1532:1532nm

1550:1550nm

1650:1650nm

1742:1742nm

SO: Port Structure

12:1x2

22: 2x2

CR♥: 0199: 1:99

1090: 10:90

2575:25:75

5050: 50:50

☆: Pigtail Length

05:0.5m

1:1m

10:10m

B: Bare Fiber

9: 900um Loose Tube

20: 2mm Loose Tube

30: 3mm Loose Tube

XX: Fiber and Connector Type

PA=PM Fiber+ FC/APC

PP=PM Fiber+ FC/PC

PN=None No connector

